

STREAMING

Micro Guidewire

STREAMING 14

Micro Guidewire

Streaming 0.014" (0.36mm) Micro guide wire is designed for advanced vessel selectivity.

Tapered tip

The tip is tapered to 0.012inch (0.31mm) for super-selective approach to the distal vasculatures.

Platinum coil

Distal 12cm platinum coil facilitates clear visibility under fluoroscopy.

STREAMING 18

Micro Guidewire


Streaming 0.018" (0.46mm) Micro guide wire is designed for High-Flow Micro-catheter delivery.

0.018" (0.46mm) Outer diameter

Minimizes the gap between Micro guide wire and High-Flow Micro-catheter which provides exceptional trackability.

Joint-less spring coil

Enables smooth trackability and advanced mobility in tortuous anatomy.




Hydrophilic coating

Enhances lubricity to allow smooth catheter control through tortuous anatomy.

Flat ribbon structure

Creates good shape memory and easy reshaping.




Flexible tip


Atraumatic to vessel wall, enables smooth insertion of the wire.

One-piece core wire

Provides excellent torque response and facilitates steerability.



Structure & ordering information



STREAMING 14

Micro Guidewire

| Catalog No. | Usable length | Flexible length | O.D. of tip | O.D. of shaft | Spring coil length | Radiopaque segment | Hydrophilic coating | Tip shape |
|--------------|---------------|-----------------|----------------------|----------------------|--------------------|--------------------|---------------------|------------|
| STM135-14S | 135cm | 37cm | 0.31mm / 0.012inches | 0.36mm / 0.014inches | 12cm | 12cm | 135cm | Straight |
| STM165-14S | 165cm | 37cm | 0.31mm / 0.012inches | 0.36mm / 0.014inches | 12cm | 12cm | 165cm | Straight |
| STM180-14S | 180cm | 37cm | 0.31mm / 0.012inches | 0.36mm / 0.014inches | 12cm | 12cm | 180cm | Straight |
| STM180-14A4S | 180cm | 37cm | 0.31mm / 0.012inches | 0.36mm / 0.014inches | 12cm | 12cm | 180cm | Angled 45° |

STREAMING 18

Micro Guidewire

| Catalog No. | Usable length | Flexible length | O.D. of tip and shaft | Spring coil length | Radiopaque segment | Hydrophilic coating | Tip shape |
|-------------|---------------|-----------------|-----------------------|--------------------|--------------------|---------------------|-----------|
| STM080-18S | 80cm | 39cm | 0.46mm / 0.018inches | 20cm | 4.5cm | 80cm | Straight |
| STM135-18S | 135cm | 39cm | 0.46mm / 0.018inches | 20cm | 4.5cm | 135cm | Straight |
| STM165-18S | 165cm | 39cm | 0.46mm / 0.018inches | 20cm | 4.5cm | 165cm | Straight |
| STM180-18S | 180cm | 39cm | 0.46mm / 0.018inches | 20cm | 4.5cm | 180cm | Straight |